



QUICKSET DETAILS WITH NO UNDERSLAB INSULATION - 300 SERIES


Sheet Index			
Detail	Layout Name	Issued	Revision/Date
QS 300-85-001	QUICKSET TAPER 385/00 WITH POLY POD	<input type="checkbox"/>	CodeMark Rev J, February 2024
QS 300-85-002	QUICKSET ULTRA 385/00 WITH POLY POD	<input type="checkbox"/>	CodeMark Rev J, February 2024
QS 300-85-003	QUICKSET REBATE 120/385/00 WITH POLY POD (90 FRAMING)	<input type="checkbox"/>	CodeMark Rev J, February 2024
QS 300-85-004	QUICKSET REBATE 120/385/00 WITH POLY POD (140 FRAMING)	<input type="checkbox"/>	CodeMark Rev J, February 2024
QS 300-85-009	QUICKSET TAPER 385/00 THERMAL BREAK WITH POLY POD	<input type="checkbox"/>	CodeMark Rev J, February 2024
QS 300-85-011	QUICKSET ULTRA 385/00 THERMAL BREAK WITH POLY POD	<input type="checkbox"/>	CodeMark Rev J, February 2024



**QUICKSET TAPER 385/00**  
**WITH 300mm POYSTYRENE POD**


**DETAIL**  
**QS 300-85-001**






**QUICKSET REBATE 120/385/00 WITH  
300mm POLYSTYRENE POD (90 FRAMING)**

**DETAIL  
QS 300-85-003**




**QUICKSET REBATE 120/385/00 WITH 300mm  
POLYSTYRENE POD (140 FRAMING)**

**DETAIL  
QS 300-85-004**



**QUICKSET TAPER 385/00 THERMAL BREAK**  
**WITH 300mm POLYSTYRENE POD**

**DETAIL**  
**QS 300-85-009**



**QUICKSET ULTRA 385/00 THERMAL BREAK**  
**WITH 300mm POLYSTYRENE POD**

**DETAIL**  
**QS 300-85-011**